

## Memocab™

For wiring



Marking system with closed ring  
High resistance in very aggressive environments

| Pack                                         | Cat. No. | Marker-holders for wiring |      |        |      |
|----------------------------------------------|----------|---------------------------|------|--------|------|
|                                              |          | Section (mm²)             |      | Ø (mm) |      |
|                                              |          | min.                      | max. | min.   | max. |
| <b>Length of marking: 15 mm (6 markers)</b>  |          |                           |      |        |      |
| 1000                                         | 379 30   | 0.25                      | 1.5  | 1.3    | 3.5  |
| 1000                                         | 379 31   | 0.75                      | 4    | 2.3    | 4.8  |
| 500                                          | 379 32   | 4                         | 16   | 4.2    | 7.6  |
| <b>Length of marking: 18 mm (7 markers)</b>  |          |                           |      |        |      |
| 1000                                         | 379 36   | 0.25                      | 1.5  | 1.3    | 3.5  |
| 1000                                         | 379 37   | 0.75                      | 4    | 2.3    | 4.8  |
| 500                                          | 379 38   | 4                         | 16   | 4.2    | 7.6  |
| 500                                          | 379 33   | 16                        | 50   | 7.6    | 12.5 |
| 200                                          | 379 34   | 50                        | 95   | 12.5   | 19   |
| 100                                          | 379 35   | 95                        | 300  | 19     | 29.5 |
| <b>Length of marking: 30 mm (12 markers)</b> |          |                           |      |        |      |
| 500                                          | 379 40   | 0.25                      | 1.5  | 1.3    | 3.5  |
| 500                                          | 379 41   | 0.75                      | 4    | 2.3    | 4.8  |
| 200                                          | 379 42   | 4                         | 16   | 4.2    | 7.6  |
| 200                                          | 379 43   | 16                        | 50   | 7.6    | 12.5 |
| <b>Length 500 mm (to be cut)</b>             |          |                           |      |        |      |
| 10                                           | 379 44   | 0.75                      | 4    | 2.3    | 4    |

| Marker-holders for simultaneous marking of both ends |        |               |      |        |      |
|------------------------------------------------------|--------|---------------|------|--------|------|
| Pre-cut label holders in rolls                       |        |               |      |        |      |
| <b>Length of marking: 18 mm (7 markers)</b>          |        |               |      |        |      |
|                                                      |        | Section (mm²) |      | Ø (mm) |      |
|                                                      |        | min.          | max. | min.   | max. |
| 1000                                                 | 379 20 | 0.25          | 1.5  | 1.3    | 3.5  |
| 1000                                                 | 379 21 | 0.75          | 4    | 2.3    | 4.8  |
| 500                                                  | 379 22 | 4             | 16   | 4.2    | 7.6  |
| 500                                                  | 379 10 | 0.25          | 1.5  | 1.3    | 3.5  |
| 500                                                  | 379 11 | 0.75          | 4    | 2.3    | 4.8  |

### Marker-holders for cables

| Pack | Cat. No. | Fixing with Colring cable ties                                           |
|------|----------|--------------------------------------------------------------------------|
| 100  | 377 12   | Length of marking: 20 mm (8 markers or 1 marker Logicab 2 Cat.No 385 05) |

### Marker-holders for all devices

| Pack | Cat. No. | Length of marking: 17.5 mm (7 markers) |
|------|----------|----------------------------------------|
| 100  | 377 10   | Adhesive                               |

| Pack | Cat. No. | Accessories                                                                              |
|------|----------|------------------------------------------------------------------------------------------|
| 1    | 379 91   | <b>Double dispenser board</b><br>For 48 strips of markers (supplied empty)               |
|      |          | <b>Selecting prong</b><br>For selecting the markers and placing them in the label holder |
| 10   | 379 90   | For 30 mm marker holders                                                                 |
| 10   | 379 92   | For 15 mm marker holders                                                                 |
| 10   | 379 89   | Double for 30 or 18 mm marker holders (for simultaneous marking of both ends)            |
|      |          | <b>Extractor</b><br>For 15 mm marker holders                                             |
| 10   | 379 93   |                                                                                          |

| Pack | Cat. No. | Marking kit to use on site                                                                                                                                                                                                                                                                 |
|------|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1    | 379 99   | <b>Composition</b><br>• 1 dispenser board Cat.No 379 91<br>• 2 selecting prongs Cat. No. 379 90/92<br>• 1 extractor Cat.No 379 93<br>• 50 label holders (0.25 - 1.5mm)<br>• 50 label holders (0.75 - 4mm)<br>• 20 label holders (4 - 16mm)                                                 |
| 1    | 379 94   | <b>Composition</b><br>Same as 379 99 plus:<br>complete with markers<br>0 to 9, A to Z and symbols<br>• 1 selecting prong Cat.No 379 89<br>• 4 strips 0 - 9 (96)<br>• 1 strip A - Z (24)<br>• 1 strip symbols (24)<br>Cat. No. 379 94 also referred to as Cat. No. 379 999 previous to 2006 |

## Memocab™ For wiring (continued)



378 01 to 378 10

378 05 + 2 x 378 06 + 378 01 +  
378 10 + 378 09 + 378 08  
in a label holder Cat.No 379 38

| Pack | Cat. No. | Markers                                               |
|------|----------|-------------------------------------------------------|
|      |          | <b>Numbers on colour background</b>                   |
|      |          | Black or white marking<br>(international colour code) |
| 600  | 378 01   | Purple 7                                              |
| 600  | 378 02   | Orange 3                                              |
| 600  | 378 03   | White 9                                               |
| 600  | 378 04   | Grey 8                                                |
| 600  | 378 05   | Green 5                                               |
| 600  | 378 06   | Yellow 4                                              |
| 600  | 378 07   | Brown 1                                               |
| 600  | 378 08   | Blue 6                                                |
| 600  | 378 09   | Black 0                                               |
| 600  | 378 10   | Red 2                                                 |



378 06

|     |        |                                    |
|-----|--------|------------------------------------|
|     |        | <b>Numbers on white background</b> |
|     |        | Black marking                      |
| 600 | 377 80 | 0                                  |
| 600 | 377 81 | 1                                  |
| 600 | 377 82 | 2                                  |
| 600 | 377 83 | 3                                  |
| 600 | 377 84 | 4                                  |
| 600 | 377 85 | 5                                  |
| 600 | 377 86 | 6                                  |
| 600 | 377 87 | 7                                  |
| 600 | 377 88 | 8                                  |
| 600 | 377 89 | 9                                  |



377 85

|     |        |                                   |
|-----|--------|-----------------------------------|
|     |        | <b>Capital letters</b>            |
|     |        | Black marking on white background |
| 240 | 378 26 | A                                 |
| 240 | 378 27 | B                                 |
| 240 | 378 28 | C                                 |
| 240 | 378 29 | D                                 |
| 240 | 378 30 | E                                 |
| 240 | 378 31 | F                                 |
| 240 | 378 32 | G                                 |
| 240 | 378 33 | H                                 |
| 240 | 378 34 | I                                 |
| 240 | 378 35 | J                                 |
| 240 | 378 36 | K                                 |
| 240 | 378 37 | L                                 |
| 240 | 378 38 | M                                 |
| 240 | 378 39 | N                                 |
| 240 | 378 40 | O                                 |
| 240 | 378 41 | P                                 |
| 240 | 378 42 | Q                                 |
| 240 | 378 43 | R                                 |
| 240 | 378 44 | S                                 |
| 240 | 378 45 | T                                 |
| 240 | 378 46 | U                                 |
| 240 | 378 47 | V                                 |
| 240 | 378 48 | W                                 |
| 240 | 378 49 | X                                 |
| 240 | 378 50 | Y                                 |
| 240 | 378 51 | Z                                 |



378 30


|     |        |                                   |
|-----|--------|-----------------------------------|
|     |        | <b>Conventional symbols</b>       |
|     |        | Black marking on white background |
| 240 | 379 54 | /                                 |
| 240 | 379 55 | •                                 |
| 240 | 379 56 | +                                 |
| 240 | 379 57 | -                                 |
| 240 | 379 58 | ~                                 |
| 240 | 379 59 | =                                 |
| 240 | 379 60 | ±                                 |




379 56

## Memocab™ marking system For wiring

### ■ Installation




1. Simultaneous marking of both ends



2. Use of double selecting prong



3. Installation in double marker-holder



The double strip can be used on site, where each marker-holders of both side will be placed on conductors